

VARISPIN 4 MULTI CENTRIFUGE

Multi purpose centrifuge suitable for a variety of application at lower speed

Main Features >>>

■ Compact design with a wide range of application

Lower speed centrifuge with an optimal capacity for different application.
Mainly suitable for clinics because it can contain most blood tubes.

■ High visibility of controller

Blue LCD screen for process monitoring and
easy touch pad for operation.

■ Range of tube

Various size of tubes are available from 5ml to 100ml.



Standard Specifications >>>



Max. RPM	4,000RPM	
Max. RCF	2,689 xg(Angle Rotor)	2,987 xg(Swing Rotor)
Max. Capacity	15ml x 24	100ml x 4
Accel / Decel phase	0 ~ 5 (6set)	
Noise Level	≤60dB	
Set Time	99 min 59sec or continuous	
Time Count	From start / From set-up RPM	
Program	10 memory	
Display	Blue LCD	
RPM Range	400 to 4,000 RPM	
Power Supply	220V / 50~60Hz	
Power Consumption	1,000W	
Dimension(W x D x H)	415 x 554 x 297 mm	
Weight (without rotor)	25kg	











保吉生化學股份有限公司
BIO-CHECK LABORATORIES LTD.









台北 | (02) 2246-7799
台中 | (04) 2371-9412
台南 | (06) 238-9287
高雄 | (07) 222-9968

Order Information »



















ITEM	DESCRIPTIONS	ORDER CODE
VARISPIN 4 Set	VARISPIN 4, with rotor AL2415G, including 15ml stainless steel sleeves, 220V/50~60Hz	V4 - SET
VARISPIN 4	VARISPIN 4, without rotor, 220V/50~60Hz	V4 - MB
AL2415G	15ml x 24 fixed angle rotor with 15ml stainless steel sleeves	V4 - AR1
AL1615G	15ml x 16 fixed angle rotor with 15ml stainless steel sleeves	V4 - AR2
S4100G	100ml 4 - wing swing rotor without buckets	V4 - SR1
S650G	50ml 6 - wing swing rotor without buckets	V4 - SR2
S2G - MTP	2 - wing micro plate swing rotor	V4 - SR3










Available rotors »

AL2415G	F15A-3	F15A-5				
 <p>Fixed Angle Rotor $\angle 45^\circ$ 24 x 15ml Radius(mm) : In 131 Out 144.5</p>						
						
Volume (ml)	3	5	10	15	15 Conical	
Number per rack / rotor	24	24	24	24	24	
Adapter bore (mm)	13.5	13.5	18.0	18.0	18.0	
Max. height for use (mm)	115	139	139	120	120	
RPM	4,000	4,000	4,000	4,000	4,000	
Radius (mm)	In 111 Out 124.5	In 126.3 Out 139.8	In 126.6 Out 140.1	In 131 Out 144.5	In 125.5 Out 139	
RCF	In 1986 Out 2227	In 2259 Out 2501	In 2265 Out 2506	In 2343 Out 2585	In 2245 Out 2486	




AL1615G	F15A-3	F15A-5				
 <p>Fixed Angle Rotor $\angle 45^\circ$ 16 x 15ml Radius(mm) : 150.3</p>						
						
Volume (ml)	3	5	10	15	15 Conical	
Number per rack / rotor	16	16	16	16	16	
Adapter bore (mm)	13.5	13.5	18.0	18.0	18.0	
Max. height for use (mm)	130	152	136	136	136	
RPM	4,000	4,000	4,000	4,000	4,000	
Radius (mm)	130.3	145.6	146.0	150.3	144.8	
RCF	2.331	2.604	2.612	2.689	2.590	

Available rotors »

S4100G	B100								
 <p>Swing Out Rotor Max. RPM : 4,000 Radius(mm) : 167 Max RCF : 2,987</p>									
	S100T-1.5-6	S100T-5-5	S100T-10-4	S100T-15-3	S100T-15C-3	S100A-50	S100A-50C	S100A-85	
									
									
Capacity (ml)	1.5	5	10	15	15 Conical	50	50 Conical		
Number per rack / rotor	6/24	5/20	4/16	3/12	3/12	1/4	1/4		
Adapter bore (mm)	11.0	13.5	16	17.5	17	29.5	30	38.5	
Max. height for use (mm)	130	130	130	130	133	130	133	130	
RPM	4,000	4,000	4,000	4,000	4,000	4,000	4,000	4,000	
Radius (mm)	164	164	164	164	167	164	167	164	
RCF	2,934	2,934	2,934	2,934	2,987	2,934	2,987	2,934	

S650G	B50								
 <p>Swing Out Rotor Max. RPM : 4,000 Radius(mm) : 167 Max RCF : 2,987</p>									
	S50A-15C	S50A-15	S50A-50C						
									
									
Capacity (ml)	15 Conical	15	50 Conical	50					
Number per rack / rotor	1/6	1/6	1/6	1/6					
Adapter bore (mm)	17	17.5	30	-					
Max. height for use (mm)	126	123	126	126					
RPM	4,000	4,000	4,000	4,000					
Radius (mm)	167	164	167	167					
RCF	2,987	2,934	2,987	2,987					

Available rotors »

S2G-MTP						
						
Swing Out Rotor Max. RPM : 4,000 Radius(mm) : 112 Max RCF : 2,003						
Capacity (ml)	MTP	DWP				
Number per rack / rotor	2/4	1/2				
Adapter bore (mm)	-	-				
Max. height for use (mm)	-	-				
RPM	4,000	4,000				
Radius (mm)	112	112				
RCF	2.003	2.003				